

Base Plates • suitable on pallets DIN 55 201

1103.500



Product Description

Material


- Steel, hardened, ground

More information

Notes

Special types on request.

Drawing



* These tolerances are valid only for optional exterior stop type.
Slot spacing $70 \pm 0,01$.


Order information



System	$a_1 \times a_2$	c	d	Dimensions				For screws	y	Number of T-slots	[kg]	Art. No.
				l_1 ± 0.013	l_2	l_3	l_4					
				[mm]				[mm]	[mm]			
V70	500 x 630	60	20	200	40/35	200	200	M12	12	7 x 9	121	1103.500


Application example











Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.