

Seating Pins · pin shape

22680.0404




Product Description

To be used as solid and precise seat and stop. The pin-shaped form of this seating pin allows an application in components with narrow seating points. Bearing surface induction hardened and grounded.


Material

- Heat-treated steel, tempered, blackened

Drawing



picture 1



picture 2

Order information

l_1 ± 0.01	d_1	Dimensions				WS	Tightening torque max.	[g]	Art. No.
		d_2	l_2	l_3	d_3				
		[mm]				[mm]	[Nm]		
with male thread – picture 1									
30	M6	4	8	15	11	10	7	12	22680.0404

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.