

Ball Casters • with sheet steel housing

22750.0036



Product Description

Ball casters are module for transport systems, conveyances, to working and packing facilities. For example, parts can be easily moved, turned and controlled. As from $d_1 = 36$ fitted with an oil drenched felt seal to protect against dirt.

Material

Cap

- Steel, zinc-plated by galvanization

Housing

- Steel, zinc-plated by galvanization

Ball

- Stainless steel

More information


Further products

- Tolerance Rings

Drawing





Order information

d_1 ± 0.095	Ball diameter	d_2	Dimensions				Location hole D_1 ¹⁾ $+0.07$ [mm]	Dynamic carrying figure C [N]	 [g]	Art. No.
			h_1 ± 0.4 [mm]	h_2	h_3	h_4				
all parts zinc-plated, ball from stainless steel										
62	45	75	19	53.7	4.2	10.3	61.83	4500	739	22750.0036

¹⁾ Reference value for 2 mm sheet steel/ 5 mm aluminium (force fit)

Application example





Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.