

Ball Knobs • metal types similar to DIN 319

24561.0240



Product Description

Material


- Stainless steel 1.4305, dull blasted

More information

Notes

Supplement DIN 319 Form C about metallic versions.


Drawing



Order information

d ₁	d ₂	Dimensions			[g]	Art. No.
		d ₃ ~ [mm]	h ~	t ₁ min.		
Stainless steel						
40	M10	22	37	18	241	24561.0240

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.