


Hinges  
25165.1025



**Product Description**

The different versions cover many applications that require a low load. These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

**Material**


**Body**

- Steel, zinc-plated by galvanization, passivated


**Axis**

- Stainless steel 1.4301

**Drawing**



picture 1    picture 2    picture 3



**Order information**

Dimensions			Holding force					Art. No.				
b <sub>1</sub>	l <sub>1</sub>	b <sub>2</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>		F <sub>1</sub>	F <sub>2</sub>	F <sub>3</sub>	[g]
[mm]			~			[N]						
with bores – picture 2, Steel												
40	40	25	4.2	4	8	2	25	2000	1000	1000	33	25165.1025

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.