

## BASEPLEX insert • Nylon, white

3988.025



### Product Description

The BASEPLEX nylon insert (series 3988) with its hardness of approx. 75 Shore D is an extra hard insert. This white insert is slightly harder than the red insert and offers even greater wear resistance. It is oil and grease resistant. This insert is available in sizes ranging from D25mm to D50mm.

Product features:


- BASEPLEX nylon insert.
- White.
- Hard.
- Wear-resistant.
- Oil and grease resistant.
- Available in sizes of D25mm to D50mm.

### Material

#### Insert

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- Oil and grease resistant

### Order information

Ø	Dimensions	 [oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	Length x Width x Height [in]					
0.98	1.06 x 1.06 x 0.98	0.42	4030618304227	AAA905c002	21-04-91-06	3988.025

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.