


**Stops · ribbed**  
EH 1586.



**Product Description**

**Material**


**Inserts**

- Hard metal

**Body**

- Tool steel, hardened

**Drawing**



**Order information**

Dimensions										Art. No.
d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	b <sub>1</sub> -0.05	b <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	[g]	
<b>ribbed on both sides – picture 1</b>										
M12	12	44	22	2	44	24	21.4	13.4	402	1586.060
<b>ribbed over the entire surface, on both sides – picture 2</b>										
M12	–	40	20	–	44	–	21.4	–	395	1586.062

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.