

Retrieval Units • with sensor  
EH 22810.



**Product Description**

For retrieve a workpiece on a seating element.

The retrieval unit is always built into a seating element as a single system. By means of a simple plug-in connection, it transmits whether a part is located at a specific position, as an electrical signal.

The retrieval unit can be used in combination with various seating elements. For example, the EH 22690 pins from the Halder standard parts are suitable.

Data is transferred via a cable connection. Optionally, the retrieval signal can be transferred by radio. The version with bushing must be used to connect the retrieval unit to the radio transmitter. The retrieval unit meets the requirements of protection class IP6K7 (highly temperature-resistant and robust).

**Material**

**Cable**

- Silicone

**Sensor**

- Plastic, black

**Plug**

- Metal

**Body**

- Aluminium, blue anodised

**Body**

- Heat-treated steel, tempered, blackened

**More information**

**Notes**


Further information on request.

Erwin Halder KG is a registered electrical equipment manufacturer (WEEE-Reg. No. DE 47048902).



**Further products**

- Index Plungers, with sensor
- Pins
- Pins, with plastic bearing surface
- Radio Transmitters, for retrieval unit
- Radio Receivers, for retrieval unit
- Sensing Elements, with sensor adapter
- Sensing Elements, with actuating bolt, protected against rotating




**Drawing**




Order information


Dimensions												WS			 min.   max.		 [g]	Art. No.
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	h <sub>1</sub> min.	h <sub>1</sub> max.	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> min.	h <sub>4</sub> max.	WS <sub>1</sub>	WS <sub>2</sub>	WS <sub>3</sub>	[°C]		[g]	
[mm]												[mm]						
<b>retrieval unit with bushing – picture 1</b>																		
M 8	M 8	20.3	12	15.8	21.4	30.5	40.5	5	12	10	20.0	30	1.5	1.5	-25	85	180	<a href="#">22810.0008</a>
M12	M12	25.5	15	18.7	24.3	41.5	59.0	8	15	10	27.5	36	2.0	2.0	-25	85	344	<a href="#">22810.0012</a>
<b>retrieval unit with plug – picture 2</b>																		
M 8	M 8	20.3	12	15.8	21.4	30.5	40.5	5	12	10	20.0	30	1.5	1.5	-25	85	180	<a href="#">22810.1008</a>
M12	M12	25.5	15	18.7	24.3	41.5	59.0	8	15	10	27.5	36	2.0	2.0	-25	85	408	<a href="#">22810.1012</a>

Accessories

	 [g]	Art. No.
<b>sensor with bush and silicone cable</b>		
	99	<a href="#">22810.9001</a>
<b>sensor with plug and silicone cable</b>		
 No Photo available	96	<a href="#">22810.9002</a>

Application example





## Compliance

For detailed compliance information please select the desired article number.