

SIMPLEX soft-face mallets • Plastic / soft metal; with cast iron housing and high-quality wooden handle

EH 3069.



Product Description

The SIMPLEX series 3069 comes with the insert combination of plastic / soft metal. The red plastic insert (series 3206) is hard and also oil and grease resistant. Made of aluminium, the silver soft metal insert (series 3209) is hard, heat-resistant and a replacement for a classic lead hammer. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with the insert combination of plastic (red, hard, oil and grease resistant) / soft metal (silver, hard, heat-resistant).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

Application Areas

Mould construction, plant construction, assembly and repair work in the automotive and truck sector

Material

Handle

- Wood

insert 1

- Plastic, red
- hard
- Oil and grease resistant
- Universal

insert 2

- Soft metal, silver
- hard
- Heat-resistant

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	12.77	4030618302537	AAA905c002	21-04-09-16	3069.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	24.13	4030618302544	AAA905c002	21-04-09-16	3069.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	44.45	4030618302551	AAA905c002	21-04-09-16	3069.050
2.36	5.91	15.94	15.94 x 5.91 x 2.36	60.57	4030618304654	AAA905c002	21-04-09-16	3069.060

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.