

## MAXXCRAFT Hickory handle • for MAXXCRAFT locksmith's hammer

EH 3266.



### Product Description

#### Material


- Handle**
- Hickory

#### More information

#### Notes

Ergonomically shaped, varnished, very robust

### Order information

Suitable for		Dimensions Length x Width x Height [in]	 [oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
MaxxCraft 300	10.43	10.43 x 1.30 x 0.93	3.53	4030618303190	EAC428c022	21-04-91-06	<a href="#">3266.003</a>
MaxxCraft 500	11.02	11.02 x 1.38 x 0.98	4.23	4030618303206	EAC428c022	21-04-91-06	<a href="#">3266.005</a>
MaxxCraft 800	12.01	12.01 x 1.50 x 1.06	6.00	4030618303213	EAC428c022	21-04-91-06	<a href="#">3266.008</a>
MaxxCraft 1000	12.20	12.20 x 1.52 x 1.08	6.35	4030618303220	EAC428c022	21-04-91-06	<a href="#">3266.010</a>

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.  
<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.