

SIMPLEX soft-face mallets • Superplastic; with reinforced cast iron housing and fibre-glass handle EH 3707.



Product Description

The SIMPLEX series 3707 is equipped with the superplastic insert on either side. This Halder top seller is a medium hard plastic insert made of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable.

The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force.

Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D80mm and as a sledge hammer (3707.081).

Product features:

- SIMPLEX soft-face mallet with superplastic inserts on both sides (white, medium hard, very durable).
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm and as a sledge hammer.

Application Areas

Gardening and landscaping, paving, curbstone setting, fence construction, driving steel wedges, scaffold construction, tent construction, sheet-metal forming, prefabricated house construction, joiner's work, carpenter's work, assembly of sharp-edged workpieces

Material

Handle

- Fibreglass with rubber grip

Inserts

- Superplastic, white
- Medium hard
- Very durable
- Wear-resistant

Housing

- Reinforced cast iron, black

Order information

Ø	Dimensions		Length x Width x Height	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	[in]	[in]						
1.18	3.54	11.81	11.81 x 3.54 x 1.34	15.87	4030618303497	AAA905c002	21-04-09-16	3707.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	30.34	4030618303503	AAA905c002	21-04-09-16	3707.040
1.97	5.31	13.19	13.19 x 5.31 x 1.97	42.33	4030618303510	AAA905c002	21-04-09-16	3707.050
2.36	5.91	16.14	16.14 x 5.91 x 2.68	61.73	4030618303527	AAA905c002	21-04-09-16	3707.060
3.15	6.89	19.29	19.29 x 6.89 x 3.15	114.29	4030618303534	AAA905c002	21-04-09-16	3707.080

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.