

## SIMPLEX soft-face mallets • Plastic / superplastic; with reinforced cast iron housing and fibre-glass handle

### 3767.030



#### Product Description

The SIMPLEX series 3767 comes with the insert combination of plastic / superplastic. The red plastic insert (series 3206) is hard and also oil and grease resistant. Composed of extruded and extremely homogeneous material, the superplastic insert (series 3207) is a medium hard plastic insert that is considerably more wear-resistant and durable. The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force. Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture). In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes D30mm to D60mm.

#### Product features:

SIMPLEX soft-face mallet with the insert combination of plastic (red, hard, oil and grease resistant) / superplastic (white, medium hard, very durable).

- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D30mm to 60mm.

#### Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

#### Material

##### Handle

- Fibreglass with rubber grip

##### insert 1

- Plastic, red
- hard
- Oil and grease resistant
- Universal

##### insert 2

- Superplastic, white
- Medium hard
- Very durable
- Wear-resistant

##### Housing

- Reinforced cast iron, black

#### Order information

| Ø    | Dimensions |       | Length x Width x Height | [oz]  | GTIN          | proficl@ss<br>5.0 | ecl@ss 10.1 | Art. No. |
|------|------------|-------|-------------------------|-------|---------------|-------------------|-------------|----------|
|      | [in]       | [in]  |                         |       |               |                   |             |          |
| 1.18 | 3.54       | 11.81 | 11.81 x 3.54 x 1.34     | 15.77 | 4030618306290 | AAA905c002        | 21-04-09-16 | 3767.030 |

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.