

Radio Transmitters • for retrieval unit

EH 22810.



Product Description

For cable-free transfer of the retrieval signal.  
The radio transmitter is installed close to the retrieval unit, and connected to the bushing of the silicone cable. The transmitter makes the polled signal available by radio, and does not require additional cable connection. Power is supplied by a battery.  
The radio transmitter meets the requirements of protection class IP 67 (robust material) and is therefore suitable for use with cooling lubricants.  
Frequency: 868.3 MHz (EU, Switzerland)  
Other frequencies available on request.



More information


Notes

An AA battery (3.6 V) is required for operation (not included in the scope of delivery). Please note the battery voltage 3.6 V!  
Further information on request.

Further products

- Radio Receivers, for retrieval unit



Drawing



Order information

Dimensions									For art. no.	[g]	Art. No.
$l_2$	$b_2$	$h_2$	$b_1$	$d_1$	$d_2$	$h_1$	$l_1$	[mm]			
universal radio transmitter with protective caps											
98	64	52.5	36	M12 x 1	4.5	37	86		22810.0008 / .0012	288	22810.9010

Accessories

	 [g]	Art. No.
<b>protection cap</b>		
	4.9	<a href="#">22810.9011</a>

Compliance

For detailed compliance information please select the desired article number.