

Nuts for T-Slots · rhombus, semi-finished

EH 23020.




Product Description

Nuts for T-slots "rhombus" do not have to be inserted lengthwise, but can be inserted directly into the slot.

Material

- Heat-treated steel, bright

Drawing



Order information

T-slot size [mm]	Dimensions				[g]	Art. No.
	a	e [mm]	h	k		
6	5.7	10	8	4	3.2	23020.0561
8	7.6	13	10	6	7.1	23020.0581
10	9.6	15	12	6	13.0	23020.0601
12	11.6	18	14	7	21.0	23020.0621
14	13.6	22	16	8	35.0	23020.0641
16	15.6	25	18	9	69.0	23020.0661
18	17.6	28	20	10	73.0	23020.0681
20	19.6	32	24	12	143.0	23020.0701
22	21.6	35	28	14	158.0	23020.0721
28	27.6	44	36	18	324.0	23020.0781
36	35.5	54	44	22	635.0	23020.0861

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.