

## SIMPLEX soft-face mallets • TPE-mid; with cast iron housing and high-quality wooden handle EH 3003.



### Product Description

The SIMPLEX series 3003 is equipped with the TPE-mid insert on either side. This grey, medium hard insert (series 3203) allows for an impact force that is comparable to the black insert made of rubber composition (series 3202). The difference is that it will not leave any undesired black marring. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D80mm, whereby the D80mm version is also available with an extra short handle (Art. 3003.082).

#### Product features:

- SIMPLEX soft-face mallet with TPE-mid inserts (grey, medium hard, no marring) on both sides.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D80mm.
- D80mm available with an extra short handle (3003.082)

### Application Areas

For delicate materials gardening and landscaping, natural stone setting, drywall construction, furniture assembly, floor tiling, paving, masonry and stair work, window and door construction, joiner's work

### Material

#### Handle

- Wood

#### Inserts

- TPE-mid, grey
- Non-marring
- Medium hard

#### Housing

- Cast iron

### Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	11.82	4030618300090	AAA905c002	21-04-09-16	3003.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	21.16	4030618300106	AAA905c002	21-04-09-16	3003.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	37.74	4030618300113	AAA905c002	21-04-09-16	3003.050
2.36	5.91	15.94	15.94 x 5.91 x 2.36	50.09	4030618300120	AAA905c002	21-04-09-16	3003.060
3.15	6.89	19.29	19.29 x 6.89 x 3.15	96.83	4030618312284	AAA905c002	21-04-09-16	3003.080

Application example



## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.