

## SIMPLEX soft-face mallets • Rubber composition / soft metal; with cast iron housing and high-quality wooden handle EH 3029.



### Product Description

The SIMPLEX series 3029 comprises the insert combination of rubber composition / soft metal. Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer. Made of aluminium, the silver soft metal insert (series 3209) is hard, heat-resistant and a replacement for a classic lead hammer. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D80mm, in size D60mm and D80mm also with rubber insert and "stand-up".

Product features:

- SIMPLEX soft-face mallet with the insert combination of rubber composition (black, medium hard, impact cushioning, odourless, low-wear) / soft metal (silver, hard, heat-resistant).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm, in size D60mm and D80mm with rubber insert and "stand-up".
- The soft metal insert is made of aluminium and replaces standard lead hammers.

### Application Areas

Mould construction, plant construction, assembly and repair work in the automotive and truck sector

### Material

#### Handle

- Wood

#### insert 1

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

#### insert 2

- Soft metal, silver
- hard
- Heat-resistant

#### Housing

- Cast iron

### Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	13.23	4030618305682	AAA905c002	21-04-09-16	3029.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	24.69	4030618302339	AAA905c002	21-04-09-16	3029.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	42.33	4030618302346	AAA905c002	21-04-09-16	3029.050
2.36	5.91	15.94	15.94 x 5.91 x 2.36	63.49	4030618302353	AAA905c002	21-04-09-16	3029.060
3.15	6.89	19.29	19.29 x 6.89 x 3.15	123.46	4030618304555	AAA905c002	21-04-09-16	3029.080

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.