

## SIMPLEX soft-face mallets • TPE-soft; with aluminium housing and high-quality wooden handle EH 3101.



### Product Description

This SIMPLEX series 3101 is equipped with the blue TPE-soft insert (series 3201) on either side. This insert is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with TPE-soft inserts (blue, soft, no marring, strong impact cushioning) on both sides.
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

### Application Areas

For very delicate materials, gardening and landscaping, floor tiling, natural stone setting, furniture assembly, drywall construction, window and door construction, joiner's work

### Material

#### Handle

- Wood

#### Inserts

- TPE-soft, blue
- Non-marring
- Soft

#### Housing

- Aluminium Al

### Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	7.05	4030618300328	AAA905c002	21-04-09-16	3101.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	12.70	4030618300335	AAA905c002	21-04-09-16	3101.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	23.10	4030618300342	AAA905c002	21-04-09-16	3101.050
2.36	5.91	15.94	15.94 x 5.91 x 2.36	29.10	4030618300359	AAA905c002	21-04-09-16	3101.060

## Application example



## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.  
<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.