

## SIMPLEX soft-face mallets • TPE-mid; with reinforced cast iron housing and fibre-glass handle EH 3703.



### Product Description

The SIMPLEX series 3703 is equipped with the TPE-mid insert on either side. This grey, medium hard insert (series 3203) allows for an impact force that is comparable to the black insert made of rubber composition (series 3202). The difference is that it will not leave any undesired black marring.

The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force.

Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D80mm.

Product features:

- SIMPLEX soft-face mallet with TPE-mid inserts (grey, medium hard, no marring) on both sides.
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D80mm.

### Application Areas

For delicate materials gardening and landscaping, natural stone setting, drywall construction, furniture assembly, floor tiling, paving, masonry and stair work, window and door construction, joiner's work

### Material

#### Handle

- Fibreglass with rubber grip

#### Inserts

- TPE-mid, grey
- Non-marring
- Medium hard

#### Housing

- Reinforced cast iron, black

### Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.81	11.81 x 3.54 x 1.34	15.87	4030618303411	AAA905c002	21-04-09-16	3703.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	29.98	4030618303428	AAA905c002	21-04-09-16	3703.040
1.97	5.31	13.19	13.19 x 5.31 x 1.97	41.27	4030618303435	AAA905c002	21-04-09-16	3703.050
2.36	5.91	16.14	16.14 x 5.91 x 2.68	60.32	4030618303442	AAA905c002	21-04-09-16	3703.060
3.15	6.89	19.29	19.57 x 6.89 x 3.54	114.99	4030618312345	AAA905c002	21-04-09-16	3703.080

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.