

APPLICATIONS



HALDER

STRIKE A BLOW WITH MANUFACTURING QUALITY

**THE
ORIGINAL
MADE IN
GERMANY.**

#BeAnOriginalPro

Follow us:
@haldertools  

HALDER USA

HALDER, INC.

821 W College Ave
Waukesha, WI 53186

www.halderusa.com
sales@halderusa.com
(888) 395-0168

Distributed by:



103.189

GB/USA/09/2020

HALDER



german
brand
award
19
gold



THE ORIGINAL FOR PROFESSIONALS

FORESTRY TOOLS

AXE AND HAMMER IN ONE

→ CAST IRON HOUSING

High resistance to breakage and the handle-protection sleeve integrated into the cast iron housing make this axe a durable companion for daily work.

→ INSERT

Due to the special insert, the axe is suitable both for splitting and for use as a soft-face mallet.

→ HICKORY SHAFT

This type of wood has one of the highest densities of any wood, and is vibration-damping while retaining its elastic properties. In case of breakage, the long fiber structure ensures maximum safety.

→ AXE BLADE

The axe blade is die-forged, hardened and tempered, edged and polished – ready for any application.



SIMPLEX SPLITTING AXE WITH THIN SHAPE

with cast iron housing and hickory handle
incl. leather cutting protection



Splitting axe and soft-face mallet in one, axe blade drop-forged and hardened, ground and polished, solid handle-protection sleeve, insert made of superplastic, KWF-certificated, all parts are replaceabl

Application:

Perfect for splitting pinewood/coniferous wood, light wedge work, striking of wedges and wooden stakes

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3007.750	1.97	3.94	30.12	95.24

SIMPLEX SPLITTING MAUL

with cast iron housing and hickory handle
incl. leather cutting protection



Splitting maul and soft-face mallet in one, splitting insert drop-forged and hardened, with turned nose, made from high-grade carbon steel, inserts made of superplastic, solid handle-protection sleeve, KWF-certificated, all parts are replaceable

Application:

Motor manual wood harvesting, safe and material-friendly driving of steel wedges with the superplastic insert, splitting 1-metre logs, splitting felled timber with a wedge, driving of wooden stakes, gardening and landscaping

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3007.160	2.36	2.56	35.43	144.62

SIMPLEX SLEDGE HAMMERS

with cast iron housing and hickory handle



Inserts made of very durable and wear-resistant superplastic, handle and inserts replaceable

Application:

Gardening and landscaping, fence construction, driving steel wedges, scaffold construction, tent construction, roof framework

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3007.081	3.15	6.89	31.50	109.00
3007.100	3.94	7.87	39.37	183.42
3007.125	4.92	8.46	40.94	271.61
3007.141	5.51	8.46	41.14	278.66

FORESTRY SLEDGE

with flat face insert made of special nylon for very high impact



non-rebound

Perfect for driving wooden stakes and metal wedges. The inserts are very wear-resistant, noise-dampening and resisting from chipping.

ATTENTION: Steel shot is not sealed in housing and could escape if nylon face is removed. Do not use in an industrial setting or where contamination is a concern!

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3366.0S3	3.15	6.33	34.65	127.03
3366.0S5	3.94	6.89	39.37	176.43
3366.0S6	3.94	7.87	39.37	229.36

SIMPLEX SPLITTING AXE WITH WEDGE RIBS

with cast iron housing and hickory handle
incl. leather cutting protection



Splitting axe and soft-face mallet in one, axe blade drop-forged and hardened, ground and polished, solid handle-protection sleeve, insert made of superplastic, KWF-certificated, all parts are replaceable, very high splitting effect

Application:

Perfect for splitting hardwood, light wedge work, striking of wedges and wooden stakes

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3007.751	1.97	3.94	30.12	100.18

HAND AXE

incl. high-quality leather belt bag as cutting protection



Robust all-metal design made from special heat-treated steel, forged in one piece, finely ground and polished on all sides, corrosion-resistant, blade carefully hardened and ground to sharpness, hand-made, anti-slip leather handle, perfectly balanced for optimum handling

Application:

Splitting of smaller logs and kindling, for sharpening wooden stakes, rough carving tasks, useful outdoor tool for campers, hunters, off-roaders, etc.

Art. No.	 [in]	 [in]	 [oz]
3555.372	3.54	14.57	35.27

TWISTED SPLITTING WEDGE

incl. convenient transport box made of special plastic



Optimum twist of 20° gives good splitting effect, optimally usable in combination with the SIMPLEX splitting maul and the SIMPLEX sledge hammers, solid twisted splitting wedge made of forged heat-treated steel, ground strike plate with chamfer, cutting edge is ground blank, with guide groove, forged diagonal grooves and forged recessed grips on sides. Perfect in combination with the SIMPLEX splitting maul and SIMPLEX sledge hammers

Application:

Efficient and simple splitting 1-metre logs

Art. No.	 [in]	 [in]	 [oz]
3556.260	1.97	10.24	109.35

SIMPLEX DIAGNOSTIC HAMMER

Insert combination:
Rubber composition/Superplastic



For tree controller and evaluator, for tapping supposed damaged spots on trees, light weight because of aluminium housing, flexible application because of inserts with different hardness

Application:

Diagnostic hammer for tree control

Art. No.	∅ [in]	 [in]	 [in]	 [oz]
3127.030	1.18	3.54	11.61	7.05
3127.040	1.57	4.53	12.80	13.23