

## SIMPLEX soft-face mallets • TPE-soft / rubber composition; with cast iron housing and high-quality extra short wooden handle

3012.082



### Product Description

This SIMPLEX soft-face mallet comes with an extra short handle. The compact design keeps the end of the handle from hitting the ground - for instance during paving work.

The SIMPLEX series 3012 is available with the popular insert combination of TPE-soft / rubber composition.

The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality and extra short wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

Product features:

- SIMPLEX soft-face mallet D80mm with the insert combination of TPE-soft (blue, soft, no marring) / rubber composition (black, medium hard, impact cushioning, odourless, low-wear).
- Extra short handle, end of handle not hitting the ground.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

### Application Areas

Gardening and landscaping, paving, floor tiling

### Material

#### Handle

- Wood

#### insert 1

- TPE-soft, blue
- Non-marring
- Soft

#### insert 2

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

#### Housing

- Cast iron

### Order information

Ø	Dimensions			Handle version	Weight [oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	Length	Width	Height						
3.15	6.89	12.8	12.8 x 6.89 x 3.15	extra short	96.65	4030618312888	AAA905c002	21-04-09-16	3012.082

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.