

SIMPLEX soft-face mallets • Rubber composition, with "Stand-Up" / Nylon; with cast iron housing and high-quality extra short wooden handle

3028.282



Product Description

This SIMPLEX soft-face mallet comes with an extra short handle. The compact design keeps the end of the handle from hitting the ground.

Available with the insert combination of rubber composition / nylon, the SIMPLEX soft-face mallet D80mm covers an extensive range of applications and is therefore widely used in the metal working industry. This top seller made by Halder has now been developed further:

Boasting an ingenious shape, the rubber insert with "stand-up" (3202.2) allows the hammer to stand securely on its head and reduces the need to bend over, making it possible to work in a much more ergonomic and back-friendly manner. Ultra low-wear, impact cushioning and odourless, the proven rubber blend offers a much longer service life than a conventional rubber hammer.

The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. Moreover, it is also oil and grease resistant.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality and extra short wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

Product features:

- Further development of Halder's top seller: The rubber insert with "stand-up" (3202.280) ensures back-friendly working and reduces the need to bend over.
- SIMPLEX soft-face mallet D80mm with "stand-up" and the insert combination of rubber composition (black, medium hard, impact cushioning, odourless, low-wear) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- Extra short handle, end of handle not hitting the ground.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

Application Areas

Assembly of sharp-edged workpieces, housing assembly, plant construction, hall construction, steel construction, exhibition stand construction, repair and maintenance work

Material

Handle

- Wood

insert 1

- Rubber composition, black, with "Stand Up"
- Medium hard
- impact cushioning
- Odorless
- Low-wear

insert 2

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- Oil and grease resistant

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height [in]	Handle version	[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
3.15	6.89	12.8	12.8 x 6.89 x 3.15	extra short	99.83	4030618312987	AAA905c002	21-04-09-16	3028.282

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.