

Distance Collars • for index plungers

EH 22120.






Product Description

Distance collars adapt the thread of index plungers to different thread reaches.

Material

- Stainless steel 1.4305

Drawing






Order information

Dimensions			For index plungers size	For finish picture	🌡️ max.	📦	Art. No.
d ₁ H12	l ±0.1 [mm]	d ₂ -0.1					
8	2	10	M 8	1/2	250	0.4	22120.0632
8	3	10	M 8	1	250	0.8	22120.0633
8	4	10	M 8	1	250	0.9	22120.0634
8	6	10	M 8	1	250	1.2	22120.0636
8	8	10	M 8	1	250	2.0	22120.0638
8	10	10	M 8	1	250	2.0	22120.0640
10	2	12	M10	1/2/3	250	0.6	22120.0642
10	4	12	M10	1/2/3	250	1.1	22120.0644
10	6	12	M10	1/3	250	1.6	22120.0646
10	8	12	M10	1/3	250	2.1	22120.0648
10	10	12	M10	1/3	250	2.7	22120.0650
10	12	12	M10	1/3	250	3.0	22120.0652
12	2	14	M12	1	250	0.6	22120.0662
12	4	14	M12	1	250	2.5	22120.0664
12	6	14	M12	1	250	1.9	22120.0666
12	8	14	M12	1	250	2.4	22120.0668
12	2	17	M12	3/4	250	2.0	22120.0672
12	4	17	M12	3/4	250	3.4	22120.0674
12	5	17	M12	3/4	250	4.4	22120.0675
16	4	17	M16	1	250	0.9	22120.0676

d ₁ H12	Dimensions		For index plungers size [mm]	For finish picture	max. [°C]	[g]	Art. No.
	l ±0.1 [mm]	d ₂ -0.1					
16	6	17	M16	1	250	1.2	22120.0677
16	8	17	M16	1	250	1.4	22120.0678
16	10	17	M16	1	250	2.0	22120.0679
16	12	17	M16	1	250	2.1	22120.0680
16	2	19	M16	3/4	250	1.3	22120.0682
16	4	19	M16	3/4	250	2.8	22120.0684
16	6	19	M16	3/4	250	3.8	22120.0686
16	8	19	M16	3/4	250	4.8	22120.0688
16	10	19	M16	3	250	6.1	22120.0690
16	12	19	M16	3	250	7.3	22120.0692
20	6	22	M20	1/3	250	3.0	22120.0693
20	8	22	M20	1/3	250	4.0	22120.0694
20	10	22	M20	1/3	250	4.9	22120.0695
20	12	22	M20	1/3	250	5.9	22120.0696
20	14	22	M20	1/3	250	6.9	22120.0697
20	16	22	M20	1/3	250	9.3	22120.0698
20	18	22	M20	1/3	250	9.0	22120.0699

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.