

SIMPLEX soft-face mallets • Plastic; with cast iron housing and high-quality wooden handle

EH 3006.



Product Description

The SIMPLEX series 3006 is equipped with the plastic insert on either side. This red insert (series 3206) is hard and also oil and grease resistant. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with plastic inserts (red, hard, oil and grease resistant) on both sides.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

Material

Handle

- Wood

Inserts

- Plastic, red
- hard
- Oil and grease resistant

Housing

- Cast iron

Order information

Ø	Dimensions			[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	Length	Width	Height					
1.18	3.54	11.61	11.61 x 3.54 x 1.18	12.17	4030618300137	AAA905c002	21-04-09-16	3006.030
1.57	4.53	12.80	12.80 x 4.33 x 1.57	22.40	4030618300144	AAA905c002	21-04-09-16	3006.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	39.51	4030618300151	AAA905c002	21-04-09-16	3006.050
2.36	5.91	15.94	15.94 x 5.71 x 2.36	53.62	4030618300168	AAA905c002	21-04-09-16	3006.060

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.