

SIMPLEX soft-face mallets • Soft metal; with cast iron housing and high-quality wooden handle EH 3009.



Product Description

The SIMPLEX series 3009 is equipped with the soft metal insert on either side. Made of aluminium, the silver insert (series 3209) is hard, heat-resistant and a replacement for a classic lead hammer. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D80mm and as a sledge hammer (3009.081).

Product features:

- SIMPLEX soft-face mallet with soft metal inserts (silver, hard, heat-resistant) on both sides
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm and as a sledge hammer.

Application Areas

For high impact, straightening work, mould construction, plant construction, assembly, repair and maintenance work

Material

Handle

- Wood

Inserts

- Soft metal, silver
- hard
- Heat-resistant

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height [in]	[oz]	GTIN	proficel@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	14.11	4030618300274	AAA905c002	21-04-09-16	3009.030
1.57	4.53	12.80	12.80 x 4.53 x 1.57	26.46	4030618300281	AAA905c002	21-04-09-16	3009.040
1.97	5.31	14.57	14.57 x 5.31 x 1.97	48.68	4030618300298	AAA905c002	21-04-09-16	3009.050
2.36	5.91	15.94	15.94 x 5.91 x 2.36	68.78	4030618300304	AAA905c002	21-04-09-16	3009.060
3.15	6.89	19.29	19.29 x 6.89 x 3.15	136.16	4030618300311	AAA905c002	21-04-09-16	3009.080

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.