

SIMPLEX soft-face mallets • Superplastic; with aluminium housing and high-quality wooden handle

EH 3107.



Product Description

The SIMPLEX series 3107 is equipped with the superplastic insert on either side. This Halder top seller is a medium hard plastic insert made of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable.

The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with superplastic inserts on both sides (white, medium hard, very durable).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

Application Areas

Gardening and landscaping, paving, curbstone setting, fence construction, driving steel wedges, scaffold construction, tent construction, sheet-metal forming, prefabricated house construction, joiner's work, carpenter's work, assembly of sharp-edged workpieces

Material

Handle

- Wood

Inserts

- Superplastic, white
- Medium hard
- Very durable
- Wear-resistant

Housing

- Aluminium Al

Order information

| Ø | Dimensions | | Length x Width x Height [in] | [oz] | GTIN | proficl@ss 5.0 | ecl@ss 10.1 | Art. No. |
|------|------------|-------|---------------------------------|-------|---------------|-------------------|-------------|----------|
| | ← | ↑ | | | | | | |
| 1.18 | 3.54 | 11.61 | 11.61 x 3.54 x 1.18 | 7.58 | 4030618300489 | AAA905c002 | 21-04-09-16 | 3107.030 |
| 1.57 | 4.53 | 12.80 | 12.80 x 4.53 x 1.57 | 12.70 | 4030618300496 | AAA905c002 | 21-04-09-16 | 3107.040 |
| 1.97 | 5.31 | 14.57 | 14.57 x 5.31 x 1.97 | 23.81 | 4030618300502 | AAA905c002 | 21-04-09-16 | 3107.050 |
| 2.36 | 5.91 | 15.94 | 15.94 x 5.91 x 2.36 | 30.16 | 4030618300519 | AAA905c002 | 21-04-09-16 | 3107.060 |

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.