

## SIMPLEX reinforced cast iron housing

EH 3711.



### Product Description

Thanks to its enlarged wall thicknesses and struts, the reinforced SIMPLEX cast iron housing (series 3711) provides for the great stability that is needed, especially during tasks that are completed with the SIMPLEX copper inserts. The increase in weight ensures greater impact force. It comes with an integrated handle protection sleeve, protecting the handle in case of mis-strikes. Robust and dampening vibrations, the housing is very durable and offers excellent break resistance - not least thanks to its wear-resistant powder coating. This black housing is available for SIMPLEX soft-face mallets with sizes ranging from D30mm to D80mm. Only fibre-glass handles may be installed into reinforced cast iron housings!

Product features:

- Reinforced SIMPLEX cast iron housing (black)
- Thicker walls and struts
- Great stability
- Also suitable for use with SIMPLEX copper inserts
- With integrated handle protection sleeve
- Excellent break resistance
- No chipping
- Vibration-dampening
- With wear-resistant powder coating
- Very durable
- Available for SIMPLEX soft-face mallets with D30mm to D80mm
- Only fibre-glass handles may be installed into reinforced cast iron housings!

### Material

#### Housing

- Reinforced cast iron, black

### Assembly

Only fibre-glass handles are allowed to be mounted in the reinforced cast iron housing!

### More information

### Notes

Including screw, nut and spring washer.

### Order information

Ø	Dimensions		[oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	Length x Width x Height [in]						
1.18	2.36 x 1.26 x 2.05		9.35	4030618301400	EAB585c005	21-04-92-30	<a href="#">3711.030</a>
1.57	2.95 x 1.77 x 2.48		18.70	4030618301417	EAB585c005	21-04-92-30	<a href="#">3711.040</a>
1.97	3.74 x 2.13 x 2.95		27.69	4030618301424	EAB585c005	21-04-92-30	<a href="#">3711.050</a>
2.36	4.21 x 2.48 x 2.91		36.16	4030618301431	EAB585c005	21-04-92-30	<a href="#">3711.060</a>
3.15	5.71 x 3.35 x 3.15		76.19	4030618301448	EAB585c005	21-04-92-30	<a href="#">3711.080</a>

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.  
<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.