

Height Adjusting Cylinders

EH 23310.



Product Description

The height adjusting cylinders can be used to extend the clamping height of down-thrust clamps EH 23310. They are also used in combination with seating pins (EH 22680.), pins (EH 22690.) and self-aligning pads (EH 22730. - EH 22741.).

Material


- Steel, case-hardened, blackened, ground

More information

Further products

- Seating Pins, ribbed or pointed
- Seating Pins, pin shape
- Pins
- Seating Pins, adjustable
- Self-Aligning Pads
- Self-Aligning Pads, with hard metal ball, ribbed
- Self-Aligning Pads, self-resetting
- Self-Aligning Pads, with hard metal ball, ribbed and self-resetting
- Self-Aligning Pads, adjustable
- Self-Aligning Pads, adjustable, self-resetting

Drawing





Order information

d ₁ -0.1	l ₁	Dimensions			WS [mm]	[g]	Art. No.
		d ₂	l ₂	l ₃			
[mm]							
picture 1							
25	20±0.01	M 8	10	-	22	75	23310.0125
25	40±0.01	M 8	20	-	22	150	23310.0126
25	80±0.01	M 8	20	-	22	306	23310.0127
32	35±0.01	M10	20	-	27	202	23310.0130
32	70±0.01	M10	20	-	27	411	23310.0132
32	140±0.01	M10	20	-	27	848	23310.0134
40	35±0.01	M12	20	-	36	336	23310.0140
40	70±0.01	M12	20	-	36	673	23310.0141
40	140±0.01	M12	20	-	36	1366	23310.0142
40	35±0.01	M16	20	-	36	331	23310.0145
40	70±0.01	M16	20	-	36	663	23310.0146
40	140±0.01	M16	20	-	36	1330	23310.0147
60	35±0.01	M12	20	-	55	765	23310.0160

d ₁ -0.1	Dimensions				WS [mm]	[g]	Art. No.
	l ₁	d ₂	l ₂	l ₃			
	[mm]						
60	70±0.01	M12	20	–	55	1533	23310.0161
60	140±0.01	M12	20	–	55	3096	23310.0162
60	35±0.01	M16	20	–	55	763	23310.0165
60	70±0.01	M16	20	–	55	1522	23310.0166
60	140±0.01	M16	20	–	55	3056	23310.0167
60	50±0.01	M20	20	–	55	1087	23310.0170
60	100±0.01	M20	20	–	55	2130	23310.0171
60	200±0.01	M20	20	–	55	4335	23310.0172
70	50±0.01	M24	25	–	65	1361	23310.0241
70	100±0.01	M24	25	–	65	2721	23310.0242
picture 2							
90	200±0.02	M24	35	50	65	8860	23310.0243
90	300±0.02	M24	35	50	65	13820	23310.0244

Application example





Compliance

For detailed compliance information please select the desired article number.