

## SIMPLEX soft-face mallets • TPE-soft / rubber composition; with aluminium housing and high-quality wooden handle EH 3112.



### Product Description

The SIMPLEX series 3112 is available with the popular insert combination of TPE-soft / rubber composition.  
The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.  
Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.  
The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily.  
Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.  
In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.  
This version is available in sizes ranging from D30mm to D60mm.

#### Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, no marring) / rubber composition (black, medium hard, impact cushioning, odourless, low-wear).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm

### Application Areas

For very delicate materials, gardening and landscaping, floor tiling, natural stone setting, furniture assembly, drywall construction, window and door construction, joiner's work

### Material

#### Handle

- Wood

#### insert 1

- TPE-soft, blue
- Non-marring
- Soft

#### insert 2

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

#### Housing

- Aluminium Al

### Order information

Ø	Dimensions		Length x Width x Height	[oz]	GTIN	proflc@ss 5.0	ecl@ss 10.1	Art. No.
1.18	3.54	11.61	11.61 x 3.54 x 1.18	7.34	4030618305194	AAA905c002	21-04-09-16	<a href="#">3112.030</a>
1.57	4.53	12.80	12.80 x 4.53 x 1.57	13.47	4030618305200	AAA905c002	21-04-09-16	<a href="#">3112.040</a>
1.97	5.31	14.57	14.57 x 5.31 x 1.97	23.81	4030618305217	AAA905c002	21-04-09-16	<a href="#">3112.050</a>
2.36	5.91	15.94	15.94 x 5.91 x 2.36	31.22	4030618305224	AAA905c002	21-04-09-16	<a href="#">3112.060</a>

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.