

## Palm Grip Screws · DIN 6335 plastic

EH 24730.



### Product Description

#### Material

##### Handle

- Thermosetting plastic PF 31, black similar to RAL 9005

##### Screw

- Steel, zinc-plated by galvanization
- Stainless steel A2

#### More information

##### Notes



Customized designs, e.g. differing lengths or screws from brass / stainless steel on request.

### Drawing



### Order information

d <sub>1</sub>	Dimensions		l	max. [°C]	[g]	Art. No.
	d <sub>2</sub> [mm]					
<b>form L, Steel</b>						
25	M 5		10	110	6.6	<a href="#">24730.0051</a>
25	M 5		15	110	7.0	<a href="#">24730.0053</a>
25	M 5		20	110	7.5	<a href="#">24730.0056</a>
25	M 5		25	110	8.1	<a href="#">24730.0058</a>
25	M 5		30	110	8.9	<a href="#">24730.0059</a>
32	M 6		15	110	11.0	<a href="#">24730.0101</a>
32	M 6		20	110	13.0	<a href="#">24730.0104</a>
32	M 6		25	110	13.0	<a href="#">24730.0106</a>
32	M 6		30	110	14.0	<a href="#">24730.0107</a>
32	M 6		40	110	16.0	<a href="#">24730.0110</a>
40	M 8		20	110	24.0	<a href="#">24730.0152</a>
40	M 8		25	110	25.0	<a href="#">24730.0154</a>
40	M 8		30	110	26.0	<a href="#">24730.0155</a>
40	M 8		40	110	30.0	<a href="#">24730.0158</a>
40	M 8		50	110	32.0	<a href="#">24730.0160</a>
50	M10		25	110	41.0	<a href="#">24730.0202</a>
50	M10		30	110	48.0	<a href="#">24730.0203</a>
50	M10		40	110	51.0	<a href="#">24730.0206</a>
50	M10		50	110	56.0	<a href="#">24730.0208</a>
50	M10		60	110	68.0	<a href="#">24730.0209</a>
63	M12		30	110	99.0	<a href="#">24730.0251</a>
63	M12		40	110	93.0	<a href="#">24730.0254</a>
63	M12		50	110	99.0	<a href="#">24730.0256</a>
63	M12		60	110	105.0	<a href="#">24730.0257</a>
63	M12		80	110	112.0	<a href="#">24730.0260</a>
80	M16		40	110	198.0	<a href="#">24730.0302</a>
80	M16		50	110	214.0	<a href="#">24730.0304</a>
80	M16		60	110	219.0	<a href="#">24730.0305</a>
80	M16		80	110	251.0	<a href="#">24730.0308</a>

d <sub>1</sub>	Dimensions		l	 max. [°C]	 [g]	Art. No.
	d <sub>2</sub> [mm]					
<b>form L, Stainless steel</b>						
25	M 5		10	110	6.6	<a href="#">24730.1051</a>
25	M 5		15	110	7.0	<a href="#">24730.1053</a>
25	M 5		20	110	7.5	<a href="#">24730.1056</a>
25	M 5		25	110	8.1	<a href="#">24730.1058</a>
25	M 5		30	110	8.9	<a href="#">24730.1059</a>
32	M 6		15	110	11.0	<a href="#">24730.1101</a>
32	M 6		20	110	13.0	<a href="#">24730.1104</a>
32	M 6		25	110	13.0	<a href="#">24730.1106</a>
32	M 6		30	110	14.0	<a href="#">24730.1107</a>
32	M 6		40	110	16.0	<a href="#">24730.1110</a>
40	M 8		20	110	24.0	<a href="#">24730.1152</a>
40	M 8		25	110	25.0	<a href="#">24730.1154</a>
40	M 8		30	110	26.0	<a href="#">24730.1155</a>
40	M 8		40	110	30.0	<a href="#">24730.1158</a>
40	M 8		50	110	32.0	<a href="#">24730.1160</a>
50	M10		25	110	41.0	<a href="#">24730.1202</a>
50	M10		30	110	48.0	<a href="#">24730.1203</a>
50	M10		40	110	51.0	<a href="#">24730.1206</a>
50	M10		50	110	56.0	<a href="#">24730.1208</a>
50	M10		60	110	68.0	<a href="#">24730.1209</a>
63	M12		30	110	99.0	<a href="#">24730.1251</a>
63	M12		40	110	93.0	<a href="#">24730.1254</a>
63	M12		50	110	99.0	<a href="#">24730.1256</a>
63	M12		60	110	105.0	<a href="#">24730.1257</a>
63	M12		80	110	112.0	<a href="#">24730.1260</a>
80	M16		40	110	198.0	<a href="#">24730.1302</a>
80	M16		50	110	214.0	<a href="#">24730.1304</a>
80	M16		60	110	219.0	<a href="#">24730.1305</a>
80	M16		80	110	251.0	<a href="#">24730.1308</a>

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.