

Threaded Lifting Pins • self-locking, with rotatable shackle

EH 22353.



Product Description

Heavy-duty lifting element for quick and easy use, with moveable, rotatable shackle and locking stud to provide protection against unintentional unlocking. For lifting loads, the threaded lifting pin is inserted into a threaded hole. In contrast to a ringbolt, time-consuming screwing in and out is therefore unnecessary. The rotatable shackle will always align with the tensile direction of pull without the pin rotating. This prevents the lifting device from being turned out of the thread and the component can be lifted safely.

All versions are corrosion-protected. The version made of stainless steel is also resistant to corrosion and weathering, so it is also suitable for external use. In addition, the high-strength, precipitation-hardened pin makes extreme loads possible.

Material

Pin part

- Heat-treated steel, tempered, manganese phosphated
- Stainless steel 1.4542, precipitation-hardened

Press button

- Aluminium, orange, anodised

Threaded element

- Stainless steel 1.4542, precipitation-hardened

Shackle

- Heat-treated steel, tempered, manganese phosphated
- Stainless steel 1.4571

Spring

- Stainless Steel

Assembly

Threaded lifting pins can be mounted into a thread that is true to gauge.

Mounting:

1. Press in the button and hold it down.
2. Insert the threaded lifting pin.
3. Release the button (The button must be back in its original position.).
4. Tighten the threaded lifting pin by hand, until it bears completely on the bearing surface.
5. It must be ensured that the threaded segments are engaged in the mounting thread.

Dismantling:

1. Unscrew the threaded lifting pin approx. a quarter of a turn anticlockwise.
2. Press in the button and hold it down.
3. Remove the threaded lifting pin.
4. Release the button.

Operation

Each threaded lifting pin contains an instruction manual with an EC Declaration of Conformity.

More information

Further products

- Lifting Pins, self-locking
- Lifting Pins, self-locking, stainless steel
- Threaded Lifting Pins, self-locking
- Threaded Lifting Pins, self-locking, for centre holes according to DIN 332
- Threaded Lifting Pins, self-locking - INCH
- Threaded Lifting Pins, self-locking, with rotatable shackle - INCH

Drawing



Order information

Dimensions														Load capacity according to DIN EN 13155			Locating thread	Tightening torque max.	Art. No.			
d ₁	l ₁	d ₂	d ₃	d ₄	d ₅	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈	l ₉	l ₁₀	F ₁	F ₂				F ₃	max.	max.
[mm]														[kN]			[mm]	[°C]	[Nm]			
Heat-treated steel																						
M 8	12	6.62	20	38	33.5	17.8	25.7	54.9	42.5	46	68	123.7	38	8	2.1	0.9	0.8	M 8	250	2	677	22353.0008
M10	14	8.35	20	38	33.5	20.0	25.7	54.9	42.5	46	68	123.7	38	10	3.9	1.5	1.5	M10	250	2	691	22353.0010
M12	17	10.07	20	38	33.5	24.0	25.7	54.9	42.5	46	68	123.7	38	12	6.2	2.5	2.3	M12	250	2	694	22353.0012
M16	17	13.80	20	38	33.5	24.0	25.7	54.9	42.5	46	68	123.7	38	12	8.4	4.5	4.2	M16	250	2	698	22353.0016
M20	22	17.25	35	59	50.0	30.0	36.5	73.7	55.6	70	102	167.5	59	17	16.6	7.7	5.0	M20	250	3	1964	22353.0020
M24	27	20.70	35	59	50.0	36.0	42.0	79.2	55.6	70	102	173.0	59	22	18.5	11.1	8.6	M24	250	3	1860	22353.0024 ¹⁾
Stainless steel																						
M 8	12	6.62	20	38	33.5	17.8	25.7	54.9	42.5	46	68	123.7	38	8	2.1	0.9	0.8	M 8	250	2	677	22353.1008
M10	14	8.35	20	38	33.5	20.0	25.7	54.9	42.5	46	68	123.7	38	10	3.9	1.5	1.5	M10	250	2	691	22353.1010
M12	17	10.07	20	38	33.5	24.0	25.7	54.9	42.5	46	68	123.7	38	12	6.2	2.5	2.3	M12	250	2	694	22353.1012
M16	17	13.80	20	38	33.5	24.0	25.7	54.9	42.5	46	68	123.7	38	12	8.4	4.5	4.2	M16	250	2	698	22353.1016
M20	22	17.25	35	59	50.0	30.0	36.5	73.7	55.6	70	102	167.5	59	17	16.6	7.7	5.0	M20	250	3	1964	22353.1020
M24	27	20.70	35	59	50.0	36.0	42.0	79.2	55.6	70	102	173.0	59	22	18.0	11.1	8.6	M24	250	3	1984	22353.1024 ¹⁾

¹⁾ from 150°C linear decrease of the load capacity by 23%


Application example











Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.