

## Flat Knurled Thumb Screws • DIN 653 EH 24770.



### Product Description

All knurled screws are one-piece manufactured with thread up to the head (DIN-designation A).

### Material


- Steel, blackened, quality 5.8
- Stainless steel 1.4305, dull blasted

### More information

### Notes


Knurling pitch and knurling depth may differ from DIN.

### Drawing



### Order information

d <sub>1</sub>	Dimensions			k	[g]	Art. No.
	l	d <sub>2</sub>	[mm]			
<b>Steel</b>						
M 3	6	12		2.5	2.3	24770.0072
M 3	8	12		2.5	2.4	24770.0073
M 3	10	12		2.5	2.5	24770.0074
M 3	16	12		2.5	2.7	24770.0077
M 3	20	12		2.5	2.9	24770.0079
M 4	8	16		3.5	5.6	24770.0092
M 4	10	16		3.5	5.7	24770.0093
M 4	12	16		3.5	6.1	24770.0094
M 4	16	16		3.5	6.2	24770.0096
M 4	20	16		3.5	6.6	24770.0098
M 4	25	16		3.5	7.1	24770.0100
M 5	10	20		4.0	10.0	24770.0112
M 5	12	20		4.0	11.0	24770.0113
M 5	16	20		4.0	12.0	24770.0115
M 5	20	20		4.0	12.0	24770.0117
M 5	25	20		4.0	12.0	24770.0119
M 5	30	20		4.0	13.0	24770.0121
M 6	12	24		5.0	18.0	24770.0132
M 6	16	24		5.0	20.0	24770.0134
M 6	20	24		5.0	21.0	24770.0136
M 6	25	24		5.0	21.0	24770.0138
M 6	30	24		5.0	22.0	24770.0140

d <sub>1</sub>	Dimensions			k	 [g]	Art. No.
	l	[mm]				
M 6	40		24	5.0	23.0	<a href="#">24770.0142</a>
M 8	16		30	6.0	36.0	<a href="#">24770.0152</a>
M 8	20		30	6.0	37.0	<a href="#">24770.0154</a>
M 8	25		30	6.0	39.0	<a href="#">24770.0156</a>
M 8	30		30	6.0	40.0	<a href="#">24770.0158</a>
M 8	35		30	6.0	42.0	<a href="#">24770.0160</a>
M 8	40		30	6.0	44.0	<a href="#">24770.0161</a>
M10	20		36	8.0	71.0	<a href="#">24770.0172</a>
M10	25		36	8.0	72.0	<a href="#">24770.0174</a>
M10	30		36	8.0	76.0	<a href="#">24770.0176</a>
M10	35		36	8.0	78.0	<a href="#">24770.0178</a>
M10	40		36	8.0	80.0	<a href="#">24770.0180</a>
<b>Stainless steel</b>						
M 4	8		16	3.5	5.6	<a href="#">24770.0292</a>
M 4	10		16	3.5	5.7	<a href="#">24770.0293</a>
M 4	12		16	3.5	6.1	<a href="#">24770.0294</a>
M 4	16		16	3.5	6.2	<a href="#">24770.0296</a>
M 5	10		20	4.0	10.0	<a href="#">24770.0312</a>
M 5	12		20	4.0	11.0	<a href="#">24770.0313</a>
M 5	16		20	4.0	12.0	<a href="#">24770.0315</a>
M 5	20		20	4.0	12.0	<a href="#">24770.0317</a>
M 6	12		24	5.0	18.0	<a href="#">24770.0332</a>
M 6	16		24	5.0	20.0	<a href="#">24770.0334</a>
M 6	20		24	5.0	21.0	<a href="#">24770.0336</a>
M 6	25		24	5.0	21.0	<a href="#">24770.0338</a>
M 8	16		30	6.0	36.0	<a href="#">24770.0352</a>
M 8	20		30	6.0	37.0	<a href="#">24770.0354</a>
M 8	25		30	6.0	39.0	<a href="#">24770.0356</a>
M 8	30		30	6.0	40.0	<a href="#">24770.0358</a>
M10	20		36	8.0	71.0	<a href="#">24770.0372</a>
M10	25		36	8.0	72.0	<a href="#">24770.0374</a>
M10	30		36	8.0	76.0	<a href="#">24770.0376</a>
M10	40		36	8.0	80.0	<a href="#">24770.0380</a>

## Compliance

For detailed compliance information please select the desired article number.