

Spring Plungers • with ball and slot - INCH

2B050.0036



Product Description


To be used for positioning, indexing, locking, latching as well as for other similar pressure applications.
Spring plungers can be used for locating or for applying pressure, as a detent or for ejection.

Material

- Body**
- Free cutting steel, blackened
- Ball**
- Stainless steel, hardened
- Spring**
- Stainless steel

Characteristic

Standard spring load: no marking



More information

Notes

- Special types on request.
Spring plungers are specially tested for spring range and forces.
- This product is manufactured in INCH dimensions.


References

A conversion table can be found in the technical data following these product information pages.
Thread lock: polyamide spot coating (for details please refer to the technical appendix).
Calculation of indexing resistance, please refer to appendix - Technical Data -

Further products

- Spring Plungers, with ball and slot

Drawing



Order information

d ₁	Dimensions			Stroke s	Spring load ¹⁾		min. max.		[oz]	Art. No.	
	Thread	d ₂	l		F ₁ ~	F ₂ ~	[°F]				
[in]		[in]		[in]	[lb]						
free cutting steel, standard spring load, Without thread lock											
#8-32	0.164	2A-UNC	3/32	11/32	0.025	0.8	1.3	-22	482	0.018	2B050.0036

¹⁾ statistical average value

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.